

## UNIFROG hand dispenser

This manual dispenser is designed to apply dense and pasty materials in electronic and mechanical assembly processes. It is mostly used in repair processes where is required small quantity of dots but foremost the **easy of application** and the **ever-readiness** of materials is preferred.



The ergonomic design enables very precise dosing during repair of SMT fine pitch components or precise application of glue in mechanical assembly processes.


UNIFROG suits perfectly to 10 ml cartridges with plastic piston made by EFD. The cartridges from other manufacturers must be always checked. It is not possible to use it for cartridges with rubber piston or for cartridges with wax plug. Special designed backside suction feature helps to keep all material inside of the needle even at the end of the dosing stroke.

**Available Options:**

•stand for 2 dispensers •set of stainless needles 0.7, 0.9 and 1.2 mm •set of plastic needles 0.7, 0.9 and 1.2 mm •spare piston 1pc



inserting of  
new cartridge



pulling the piston  
into cartridge piston



adjusting of the backside  
suction intensity



proper way of  
dispensing